

FX Fusion Splice-On Connectors

Description	Belden Part Number		
	Multimode		Singlemode
	OM3/OM4 - Aqua	OM4 - Erika Violet	OS2 - Blue
LC with 900/250 µm Boot, 1/Pack	FT3LC900FS01	FT4LC900FS01	FTSLC900FS01
LC with 2 mm Boot, 1/Pack	FT3LC2MMFS01	FT4LC2MMFS01	FTSLC2MMFS01

FX Fiber Distribution Cable

# of Fibers	Belden Part Number		
	OM3	OM4	OS2
Non-terminated Plenum – Indoor			
6	FI3D006P9	FI4D006P9	FISD006P9
12	FI3D012P9	FI4D012P9	FISD012P9
24	FI3D024P9	FI4D024P9	FISD024P9
Non-terminated Plenum Armor – Indoor			
6	FI3D006A9	FI4D006A9	FISD006A9
12	FI3D012A9	FI4D012A9	FISD012A9
24	-	FI4D024A9	FISD024A9
Unitized 12-Fiber Sub-Units Plenum – Indoor			
48	-	FI4D048PK	FISD048PK
Unitized 12-Fiber Sub-Units Plenum Armor – Indoor			
48	-	FI4D048AK	FISD048AK
Non-terminated Plenum – Indoor/Outdoor			
6	FD3D006P9	FD4D006P9	FSD006P9
12	FD3D012P9	FD4D012P9	FSD012P9
24	-	FD4D024P9	FSD024P9
Non-terminated Plenum Armor – Indoor/Outdoor			
6	FD3D006A9	FD4D006A9	FSD006A9
12	FD3D012A9	FD4D012A9	FSD012A9
24	-	FD4D024A9	FSD024A9
Unitized 12-Fiber Sub-Units Plenum – Indoor/Outdoor			
48	-	-	FSD048PK
Unitized 12-Fiber Sub-Units Plenum Armor – Indoor/Outdoor			
48	-	-	FSD048AK

Standard FX Patch Cords

Length (m)	Belden Part Number		
	OM3 (Aqua)	OM4 (Erika Violet)	OS2 (Blue/Yellow)
LC Duplex Uniboot to LC Duplex Uniboot			
2	-	FP4LULU002M	-
3	-	FP4LULU003M	FPSLULU003M
LC Duplex to LC Duplex			
2	FP3LDLD002M	FP4LDLD002M	FPSLDLD002M
3	FP3LDLD003M	FP4LDLD003M	FPSLDLD003M

FX Pigtails

Description	Belden Part Number		
	OM3	OM4	OS2
Standard Pigtail Kits (Connector on 900 µm Fiber)			
LC	FT3LC900PR12	FT4LC900PR12	-
Standard Single Pigtails (Connector on 900 µm Fiber)			
LC	FT3LC900PS01	FT4LC900PS01	FTSLC900PS01

Standard FX ECX Frames

Description-Patch Ports (fibers)	Belden Part Number		
	OM3 (Aqua Adapters)	OM4 (Erika Violet Adapters)	OS2 (Blue Adapters)
LC Duplex			
12 (24)	FF3X12LD	FF4X12LD	FFSX12LD

FX ECX Housings*

Description	Number of Module Bays	Total LC Duplex using ECX Frames	Total LC Duplex using ECX Cassettes	Belden Part Number
1U Housing	2 Cassettes or Frames	32	24	ECX-01U
4U Housing	12 Cassettes or Frames	192	144	ECX-04U

*FX ECX Housings will be added to the service soon.

Questions?

Contact your local Belden representative, call us at **1.800.BELDEN.1** (1.800.235.3361) or visit www.belden.com